


DESCRIPTION: 9 POS MICRO-D FEMALE (ASSEMBLED) TO BLUNT CUT



1. P1. CONNECTOR: NORCOMP MICRO D 9S, ASSEMBLED HOOD W/THUMBSCREWS
2. P2. BLUNT CUT END
3. WIRE: 28AWG [7X36] x9C +ALUMINUM FOIL W/ BRAID 65%, UL2464+CSA, COLOR BLACK
4. PINOUT:

P1	P2
1	BLACK
2	BROWN
3	RED
4	ORANGE
5	YELLOW
6	GREEN
7	BLUE
8	VIOLET
9	GRAY
SHELL	SHIELD

P/N	$L \pm T$
CCA-009-I18R152	18±0.590in
CCA-009-I36R152	36±0.787in
CCA-009-I72R152	72±0.984in
CCA-009-M.5R152	500±15mm
CCA-009-M01R152	1000±20mm
CCA-009-M02R152	2000±25mm
CCA-009-M03R152	3000±35mm

NOTE:

**NOT DESIGNED TO MATE WITH NORCOMP 580-M // 581-M SERIES CONNECTORS. IF ANY QUESTIONS PLEASE CONTACT ENG@NORCOMP.NET

PACKAGED: 1 PER BAG

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P.JENKINS

DATE:
01/18/2012

NorComp

SCALE:
NTS


SHEET OF
1 1

REV
4

DWG NO.

CCA-009-YYYYR152

DESCRIPTION: 15 POS MICRO-D FEMALE (ASSEMBLED) TO BLUNT CUT



1. P1. CONNECTOR: NORCOMP MICRO D 15S, ASSEMBLED HOOD W/THUMBSCREWS
2. P2. BLUNT CUT END
3. WIRE: 28AWG [7X36] x15C +ALUMINUM FOIL W/BRAID 65%, UL2464, COLOR BLACK
4. PINOUT:

P1	P2
1	BLACK
2	BROWN
3	RED
4	ORANGE
5	YELLOW
6	GREEN
7	BLUE
8	VIOLET
9	GRAY
10	WHITE
11	PINK
12	LIGHT GREEN
13	BLACK WHITE
14	BROWN WHITE
15	RED WHITE
SHELL	SHIELD

P/N	L ± T
CCA-015-F18R152	216±2.952in
CCA-015-F28R152	336±3.952in
CCA-015-I18R152	18±0.590in
CCA-015-I36R152	36±0.787in
CCA-015-I72R152	72±0.984in
CCA-015-M.5R152	500±15mm
CCA-015-M01R152	1000±20mm
CCA-015-M02R152	2000±25mm
CCA-015-M15R152	15000±100mm
CCA-015-M20R152	20000±150mm
CCA-015-M30R152	30000±250mm


NOTE:

**NOT DESIGNED TO MATE WITH NORCOMP 580-M // 581-M SERIES CONNECTORS. IF ANY QUESTIONS PLEASE CONTACT ENG@NORCOMP.NET

RoHS COMPLIANT

PACKAGED: 1 PER BAG

DO NOT SCALE FROM DRAWING




THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS
DATE:
01/18/2012

NorComp

SCALE: NTS	SHEET 1	OF 1	REV 5
DWG NO.		CCA-015-YYYYR152	



- 1. P1: NORCOMP MICRO D 25S, ASSEMBLED HOOD W/THUMBSCREWS
- 2. P2. BLUNT CUT END
- 3. WIRE: 28AWG [7X36] x25C +ALUMINUM FOIL + BRAID 65%, UL2464, COLOR BLACK
- 4. PINOUT:

P1		P2
1	_____	BLACK
2	_____	BROWN
3	_____	RED
4	_____	ORANGE
5	_____	YELLOW
6	_____	GREEN
7	_____	BLUE
8	_____	VIOLET
9	_____	GRAY
10	_____	WHITE
11	_____	PINK
12	_____	LIGHT GREEN
13	_____	BLACK WHITE
14	_____	BROWN WHITE
15	_____	RED WHITE
16	_____	ORANGE WHITE
17	_____	GREEN WHITE
18	_____	BLUE WHITE
19	_____	VIOLET WHITE
20	_____	RED BLACK
21	_____	ORANGE BLACK
22	_____	YELLOW BLACK
23	_____	GREEN BLACK
24	_____	GRAY BLACK
25	_____	PINK BLACK
SHELL	_____	SHIELD

P/N	L ± T
CCA-025-I18R152	18±0.590in
CCA-025-I36R152	36±0.787in
CCA-025-I72R152	72±0.984in
CCA-025-M.5R152	500±15mm
CCA-025-M01R152	1000±20mm
CCA-025-M02R152	2000±25mm
CCA-025-F08R152	8±0.17ft
CCA-025-F10R152	10±0.17ft
CCA-025-F60R152	60±0.5ft

NOTE:

**NOT DESIGNED TO MATE WITH NORCOMP 580-M // 581-M SERIES CONNECTORS. IF ANY QUESTIONS PLEASE CONTACT ENG@NORCOMP.NET

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: P. JENKINS
		DATE: 01/18/2012

	SCALE: NTS	SHEET 1 OF 1	REV 5
	DWG NO. CCA-025-YYYYR152		